



Thermal Transfer Printable Labels - # THT-8-427-10

MATERIAL:	Self-Laminating Vinyl
SIZE:	0.500" W x 1.437" H (12.700 mm W x 36.500 mm H)
QTY/UOM:	10,000/Roll
CATALOG #:	THT-8-427-10
PRODUCT #:	30111

OVERVIEW [SPECIFICATIONS](#)

Description for Thermal Transfer Printable Labels

Printable, self-laminating vinyl labels for thermal transfer printers. Please Note: This material is UL recognized with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

Specification Of Thermal Transfer Printable Labels

Application(s): Panel Identification, Wire & Cable Marking

Agency: UL Recognized

Approval(s)/Compliance:

Size: 0.500" W x 1.437" H (12.700 mm W x 36.500 mm H)

Printable Area: 0.500" W x 0.500" H (12.700 mm W x 12.700 mm H)

Web Width: 3.350" (85.09 mm)

Label Type/Style: Self-Laminating Label

Vertical Repeat: 1.625" (41.28 mm)

Horizontal Repeat: 0.662" (16.81 mm)

Color: White/Translucent

Finish: Matte

Qty Per Row: 5

Material Type: Vinyl

Material Description: Self-Laminating Vinyl

Brady Material #: B-427

General ID Catalog: [pg. 132](#)

Recommended Ribbon Series: 4300

Suggested Ribbon Part#: R4300

Acceptable Ribbon Series: 6200, 4500 (colors)

Printer Compatibility: BBP81, Brady 1244, Brady 1344, Brady 200MVP Plus, Brady 2461, Brady 300MVP Plus, Brady 300X-Plus II, Brady 3481, Brady 360X-Plus II, Brady 600X-Plus II, Brady 6441, IP300, IP600, Tagus T200, Tagus T300, Thermal Transfer Printers

Style: Roll-Form, Radius Corners

Special Properties: Excellent abrasion and smudge resistance, Excellent water & oil resistance, Self-Extinguishing, Self-Laminating

RoHS Compatibility: Compliant with RoHS Directive. NOTE: All statements concerning RoHS Directive compliance refer to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC. Product compliance is based upon information provided by suppliers of the raw materials used by Brady to manufacture these products, or by independent laboratory testing of these products. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

QTY/UOM: 10,000/Roll