

**Vynckier Enclosure Systems, Inc.**

271 McCarty Drive Houston, Texas 77029

Telephone: (713) 374-7850 Fax: (800) 444-1261

Web site: www.EnclosuresOnline.com

**Item # ANB1208PL, ARIA ANB1208 W/ BONDED WINDOW / PL LATCHES**

**\$283.70**



**ARIA ANB1208 W/ BONDED WINDOW / PL LATCHES**

**ANBPL**

**Features**

Vynckier Enclosure Systems' standard ARIA polyester boxes range in size from 12" x 8" up to 40" x 32", 7 different sizes and a variety of configurations.

The ARIA "ANBPL" standard enclosures include 2 padlockable latches with a bonded window on the cover.

All bases are made of light grey (RAL7035) fiberglass reinforced polyester.

Furnished with four threaded studs and bolts for mounting plate or mounting frame installation.

Door bosses for front panel mounts.

Easy to install hinged Aluminum front panel.

Maintenance free and corrosion resistant.

Temperature resistance: -58°F to +302°F (-50°C to 150°C), momentary to 392°F (200°C).

Seamless polyurethane gasket in molded door edge channel.

Patented door-lifter ensuring the door takes it's center position during closing.

Self-adhesive rain-shield included as a standard accessory with each cabinet.

Easily modified with conventional tools such as a drill, milling equipment, saw or punch.

**Applications**

Contoured body provides an attractive and contemporary appearance that can be used as: insulated electrical junction boxes, terminal wiring boxes, instrument housings and housings for electrical controls in wet, dusty and corrosive environments

Ideal for high performance applications in: heavy industry - paper mills, mining sites, steel mills, lumber production, refineries, chemical plants, alimentation industry and breweries, waste-water treatment, public lighting, traffic control and signalization, shipyards and offshore oil production platforms

**Standards**

IEC 60439-1

IEC 60529

EN 60439-1

EN 60529

EN 50298

**Approvals**

UL types 3, 3R, 3S, 4, 4X, 12 and 13 per UL 508

CSA types 2, 3, 3R, 3S, 4 4X, 12 and 13

AS 3132 - 1991

**SPECIFICATIONS**

Availability	Special Modified - 14 to 28 days
ARIA Outside Height (inch)	12.4
ARIA Outside Height (mm)	315
ARIA Outside Width (inch)	8.46
ARIA Outside Width (mm)	215

ARIA Outside Depth (inch)	6.69
ARIA Outside Depth (mm)	170
ARIA Inside Height (inch)	10.83
ARIA Inside Height (mm)	275
ARIA Inside Width (inch)	6.69
ARIA Inside Width (mm)	170
ARIA Inside Depth (inch)	5.83
ARIA Inside Depth (mm)	148
ARIA Weight (lbs)	5.25
ARIA Backplate Part No. (Aluminum Steel Non-Metallic)	ABP1208A ABP1208N ABP1208S
ARIA Backplate Dimensions - H x W (inch)	9.84 x 5.91
ARIA Backplate Dimensions - H x W (mm)	250 x 150
FRP UL Type Rating	3, 3R, 4, 4X, 12, 13
Temperature Resistance (F)	-58 to +302
Temperature Resistance (C)	-50 to +150