

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [22-01-3037](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnection System](#)  
**Description:** 2.54mm Pitch KK® Crimp Terminal Housing, Friction Ramp, 3 Circuits, Use With 2759|6459|41572

**Documents:**

[3D Model](#) [Packaging Specification PK-2695-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-10-07 \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [2695](#)  
 Application Signal, Wire-to-Board  
 Overview [KK® Interconnection System](#)  
 Product Name KK®

**Physical**

Circuits (maximum) 3  
 Color - Resin Natural (White)  
 Flammability 94V-0  
 Gender Female  
 Glow-Wire Compliant No  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 2.54mm  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating 0°C to +75°C

**Material Info**

Old Part Number 2695-03RP  
 UPC 800753593831

**Reference - Drawing Numbers**

Packaging Specification PK-2695-001  
 Product Specification PS-10-07  
 Sales Drawing SD-2695



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[2695Series](#)

**Mates With**

2.54mm Pitch KK® PCB Headers [42375](#) , [42377](#) , [42376](#) , [4030](#) , [6373](#) , [6410](#)

**Use With**

[2759](#) , [4809](#) KK® Crimp terminal