

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35023-0010](#)
Status: **Active**
Description: 2.00mm Pitch Board-in Crimp Housing, 10 Circuits

Documents:

3D Model	Product Specification PS-35044-001 (PDF)
Drawing (PDF)	Packaging Specification PK-35023-001 (PDF)
Product Specification PS-35023-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	35023
Application	Signal
Product Name	Board-In

Physical

Circuits (maximum)	10
Color - Resin	Natural
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C

Material Info

UPC	800753876682
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-35023-001
Product Specification	PS-35023-001, PS-35044-001
Sales Drawing	SD-35023-*0**, SD-35023-001




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[35023Series](#)

Use With

[35044](#) , [35021](#)