

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [89400-1210](#)
Status: **Active**
Description: 2.00mm Pitch Wire-to-Board Header, Vertical, 12 Circuits, without Kinked PC Tail

Documents:

[3D Model](#) [Product Specification PS-87369-0001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family PCB Headers
 Series [89400](#)
 Application Signal, Wire-to-Board
 Product Name N/A

Physical

Breakaway No
 Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin Natural
 Durability (mating cycles max) 30
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Nylon
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 3.40mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.20mm
 Packaging Type Bag
 Pitch - Mating Interface 2.00mm
 Plating min - Mating 1.270µm
 Plating min - Termination 1.270µm
 Polarized to PCB No
 Shrouded Partial
 Stackable No
 Temperature Range - Operating -25°C to +85°C
 Termination Interface: Style Through Hole


Electrical

Current - Maximum per Contact 4A
 Voltage - Maximum 250V

Material Info

Reference - Drawing Numbers

Product Specification PS-87369-0001



EU RoHS

**ELV and RoHS
 Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[89400Series](#)

Mates With

[87369 Crimp Housing](#)

This document was generated on 06/05/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION