


MICRO D-SUB - PCB LAYOUT - DUAL PORT - 9 POSITION

PANEL CUTOUT



PANEL CUTOUT
TOLERANCE ±0.002 [±0.05]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOrComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

NorComp

DRAWN:		DATE:			
M. SIGMON				08-25-11	
CHECKED:		DATE:			
SCALE:	SHEET	OF			REV
4:1	:	2	2		1 1

ROHS COMPLIANT

DESCRIPTION:

DWG NO. 382-009-112L565