

HL Stick – The new expert for fine working

| TECHNICAL DATA | |
|-------------------------|---|
| Product code: | 004019 |
| Dimensions (h x w x d): | 780 x 760 x 2350 mm |
| Voltage: | 230 v 50 Hz |
| Output: | 350 W |
| Temperature: | 400 °C, 500 °C with reduction nozzle |
| Air Flow: | 100 l/min |
| Switches: | 1 (On/Off) |
| Specials: | Incl. LED / Stable hanging |
| Length Power Cord: | 2.20 m |
| Weight: | 572 g |
| Motor: | Brush motor |
| Heating element: | Ceramic |
| Accessories included: | 7mm reduction nozzle, reduction nozzle with protection reflector, 10mm and 40mm reflector nozzles |

Available April 2012



Trade price
£69.90 nett

Working punctual and precise with hot air!

This small ergonomically shaped hot air tool enables work in confined places as well