

XB4BD21

SELECTOR SWITCH 600VAC 1.2A XB4



List Price \$51.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	10A
Approvals	UL Listed File Number E164353 CCN NKCR - CSA Certified File Number LR44087 Class 321103 - CE Marked
Bezel Material	Chromium Plated Metal
Enclosure Type	Water tight, Dust tight and Corrosion Resistant (Indoor/Outdoor)
Enclosure Rating	NEMA 4/4X/13
Maximum Voltage Rating	600VAC
Head Type	Round
Mounting Type	Panel
Number of Positions	2
Operator Action	Maintained
Operator Type	Non-Illuminated
Size	22mm
Terminal Type	Screw Clamp
Type	XB4
Utilization Category	AC15 - DC13
Contact Configuration	1 NO
Knob Color	Black
Knob Type	Standard Lever

Shipping and Ordering

Category	22468 - Push Buttons, Metal, 22mm, ZB4, XB4
Discount Schedule	CS2
GTIN	00785901380603
Package Quantity	1
Weight	0.18 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/08/2012 04:44:38