



Miniature/Incandescent

[Item # 464]

[List View](#)  [Printer-friendly version](#)

Sample Image

| | |
|--------------------|---------------------------|
| Item Number | 464 |
| Lamp Type | Miniature |
| Desc | T3 1/4 WEDGE 28V .17A 3CP |
| Bulb Shape | T-3 1/4 |
| Max. Bulb Dia (in) | 13/32 |
| Max. Bulb Dia (mm) | 10.0 |
| Base Type | Wedge (T-3 1/4) |
| Volt | 28 |
| Amp | 0.17 |
| Watt | 4.76 |
| MSCP | 3.00 |
| Filament | C-2F |
| MOL (in) | 1.06 |
| MOL (mm) | 26.80 |
| LCL (in) | 0.56 |
| LCL (mm) | 14.20 |
| Avg Life Hrs | 1500 |
| Drawing | |
| New Product Sheet | |



Sample Image

[List View](#)