



T&B® Fittings

PRINT

Rigid/IMC Conduit Fittings

T&B Catalog Number: 370
UPC Number: 78621000370
Status: Active

Description:
 1/2" Hub Connector, Steel-Electro Zinc Plated, Nylon Insulated. For use with Rigid/IMC Conduit.

ROHS CAD SUBMITTAL PACKAGE

Where To Buy

Enter Zip Code:

Enter Quantity:

Features

- Rugged steel/malleable iron construction
- Tapered internal threads for water-tight/dust-tight union
- Threads relieved to prevent bottoming of conduit, ensuring sound assembly
- Recessed sealing ring at box end; sealing ring captivated
- Hardened steel/malleable iron/copper-free aluminum locknuts designed to provide high quality ground continuity; extended reach of locknut permits clamping on thin boxes and enclosures
- Insulated throat, insulates conductors, prevents abrasion and thinning of conductor insulation, reduces wire pull effort

General

Material: Steel
Finish: Electro Zinc Plated

Dimension Information

Hub Size (inches): 1/2
Dimension A (inches): 1 3/8
Dimension B (inches): 1 1/4
Dimension C (inches): 1/2

Packaging

Inner Package: 25
Outer Package: 100
Package Height: 6.3
Package Length: 9.6
Package Width: 8.6
T&B Sold in UOM: Each
T&B Weight Per UOM: 17.6 lbs. per 100

Application Support

[Spacing Chart](#) [Click Here](#)

Notes

*Note Available with DURA-PLATEO Finish

Certifications

RoHS Compliance Yes [Generate Compliance Certificate](#)

Certifications



File Nbr:
E 23018

HOME
[Global Site](#)
[Report Issue](#)

LOGIN
[T&B Access \(Dist only\)](#)
[Suppliers](#)
[MyTNB](#)

RESOURCES
[Catalog PDFs](#)
[End User Toolkit](#)
[Solution Set Brochures](#)
[Vertical Market Brochures](#)
[Where To Buy](#)

SUPPORT
[Contact Us](#)
[Global Locations](#)
[Product Support](#)
[Tool Services](#)
[Terms](#)

COMPANY
[About Us](#)
[Careers](#)
[Employees](#)
[News](#)

Thomas & Betts®
 © 2012 Thomas & Betts Corporation
 No material from this site may be copied, distributed or in any way used without the expressed prior permission of Thomas & Betts.