



APC Replacement Battery Cartridge #44
Part Number: RBC44



[Technical Specifications](#) [Product Overview](#) [Documentation](#) [Ratings and Reviews](#)

Batteries & Runtime

Battery Volt-Amp-Hour Capacity	960
Battery Type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof
Battery mounting	Enclosed battery cartridge
Expected Battery Life (years)	3 - 5
RBC™ Quantity	1
Replacement battery cartridge note	Each RBC44 consists of 2 battery modules.

Physical

Net Weight	34.56 KG
Maximum Height	122.00 mm
Maximum Width	197.00 mm
Maximum Depth	597.00 mm
Shipping Weight	37.28 KG
Shipping Width	409.00 mm
Shipping Height	226.00 mm
Shipping Depth	781.00 mm
Color	Black
Units per Pallet	12.00

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C