

# Scroll Extreme II

# 9.7" TABLET PC

## ANDROID™ 4.0 ICS

### IPS SCREEN

by **Storage Options**

Accessories available at  
[storageoptions.com](http://storageoptions.com)

Scroll Extreme II is a capacitive touch-screen Android™ 4.0 tablet that incorporates Bluetooth® wireless technology. Portable, with its large 9.7", highly responsive screen with IPS technology, powerful hardware and a stylish, slim design, the Scroll Extreme II is the perfect companion for internet browsing, games, videos and a host of other applications.

At the Scroll Extreme II's heart is a capable AllWinner A10 Cortex A8 1.2GHz, graphics processing 1GB RAM and 8GB of memory (with up to a further 32GB via optional Micro SD card\*) to store your content. Whether it's rich, online content, 3D games or support for major video and ebook formats that you want, Scroll Extreme II offers all this and more.

Scroll Extreme II also a highly versatile device; connect peripherals such as mice, keyboards and speakers, wirelessly and effortlessly with Bluetooth technology or watch your favourite film in full 1080p HD or 3D by connecting Scroll Extreme II to your 3D or HD TV or monitor (via an optional high-speed HDMI cable\*).

- 9.7" Android™ 4.0 Tablet PC with Bluetooth Connectivity
- Elegant Aluminium Design, with Ultra-Slim Casing
- Quick and Simple to Use
- Intuitive, IPS, Capacitive Touch-Screen
- HDMI Port for 1080p / 3D Output to Compatible TV or Monitor
- Bluetooth® Wireless Technology to Connect Peripherals (Mice / Keyboards / Speakers etc.)\*

**Part No. 55111**

**Contents - Tablet PC, Power Adaptor, USB Cable, On-The-Go Cable, Earphones and Manual.**

\*Bluetooth accessories, micro SD card and HDMI cable are available separately and not included.



Your Marketplace for android apps



**ANDROID™ 4.0 INSIDE**

# Scroll Extreme II

# 9.7" TABLET PC

## ANDROID™ 4.0 ICS

### IPS SCREEN

by **Storage Options**

Accessories available at  
[storageoptions.com](http://storageoptions.com)



#### Software

- Android™ 4.0

#### Hardware

- Processor: AllWinner A10 Cortex A8 1.2GHz, Graphics Processor
- Display: 9.7" 1074 x 768 Capacitive Multi-touch IPS Screen
- Memory: 1GB DDR3 RAM
- Internal Memory: 8GB Memory Built-in, Micro SD Card Expandable Up to 32GB
- Battery: 7800 mAh Li-Polymer Rechargeable Battery
- Camera: Front Facing 0.3 Megapixel, Back Facing 2.0 Megapixel
- G-Sensor: 16 bit G-sensor, Monitors / Rotates Screen Through 360°
- Speakers: Built-in Speaker
- Headphones: 3.5mm Earphone Jack

#### Connectivity

- Wireless Networking: Wi-Fi 802.11b/g/n
- 3G: Supports External 3G Dongles
- Bluetooth: Yes
- TV Output: HDMI TV-Output (Mini HDMI)
- Micro USB Host Port: 2x For Peripheral Connection (e.g. Keyboard, Flash Drive)
- Power: 5V-2A DC

#### Multimedia

- Video Support: Full HD 1080P Supports MKV, AVI, RM/RMVB, WMV, 3GP, MOV, MP4, ASF, MPG, DAT, VOB, FLV.
- E-Book Support: PDF, EPUB, MOBI

#### Features

- Music, Photos, Movies, E-mail, 3D Games and 1080P 3D Video Output!

#### Case

- Slim Aluminium Casing

#### Dimensions

- 242mm x 189mm x 10mm



ANDROID™ 4.0 INSIDE