

LRD3359**Overload Relay (TeSys D) Class 10 with Single Phase Sens., Trip: 48A to 65A**

List Price \$107.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.****Technical Characteristics**

For Use With	LC1D50 thru LC1D80
Marketing Trade Name	TeSys
Mounting Style	Direct
Overload Type	Thermal - Ambient Compensated Bi-Metallic/Differential
Trip Class	Class 10 with Single Phase Sensitivity
Thermal Trip Setting	48A to 65A
Terminal Type	Screw Clamp
Type	TeSys D

Notes:

Direct mount to old D2 style D40 to D80 only (no Everlink terminations)

Shipping and Ordering

Category	22347 - Contactors, IEC, Overloads, TeSys
Discount Schedule	I12
GTIN	00785901208310
Package Quantity	1
Weight	1.07 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	FR

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.