
FLOW SENSORS

FT-110 - TurboFlow® Economic Flow Rate Sensor

Part No. 173934



Sensor Type	TurboFlow
Standard Flow Range (GPM)	0.26 - 4.0
Flow Range (GPM)	0.26 - 4.0
Body Material	Nylon 12
Port Size	3/8" NPT Male
Input Power	5 VDC to 24 VDC @ 8mA
Output	NPN Sinking Open Collector @ 20mA, max.
Low Flow Accuracy	±3%
Standard Flow Accuracy	±3%
Maximum Pressure (PSI)	200
Minimum Temperature (°F)	-4
Maximum Temperature (°F)	212.000
Electrical Termination	Spade Terminals (0.110"/0.248"X .031")
Wetted Materials	Nylon 12, PTFE (15% Graphite)
Recommended Filtration	50 micron
Minimum Qty (per Release)	1
Weight (LBS)	0.0625