

BNC Plug Clamp, 75R




Specifications:


Connector Type	: BNC Coaxial
Body Style	: Straight Plug
Coaxial Termination	: Clamp
Impedance	: 75Ω
Frequency Max	: 11GHz
Connector Mounting	: Cable
Body Plating	: Nickel
Cable Diameter Max	: 5.8mm
Coaxial Type	: UR70
Contact Resistance	: 1.5mΩ
DC Current Max	: 1A
Operating Temperature	: -65°C to +165°C
Proof Voltage	: 2kV
VSWR	: 1.35
Working Voltage	: 500V
Bodies	: Brass per JIS-C3604
Centre Contact	: Brass per JIS-C3604
Insulation	: PTFE per ASTM D1457 and ASTM D1710

Part to be clean and free of burrs

BNC Plug Clamp, 75R



Dimensions : Millimetres (Inches)



Stripping Dimension

Number	Description	Material	Finish
1	Shell	Zinc	Nickel 100 μ " Min.
2	Body	Brass	
3	Insulation	PTFE	None
4	Gasket	Rubber	
5	Washer	Brass	Nickel 100 μ " Min.
6	Spring Washer	SK-5	
7	Washer	Brass	
8	Braid Clamp		
9	Gasket	Rubber	None
10	Washer	Brass	Nickel 100 μ " Min.
11	Nut		
12	Centre Contact		Gold

Part Number Table

Description	Part Number
Plug, BNC, Clamp, 75R, UR70, NI	13-01-3 TGN UR70

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicom is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com

