



RBK SLT CSK MTS A2 SS M6X25 (PK 100)

Din 963 Grade A2 stainless steel machine screws

Slotted drive with a countersunk head, fully threaded

Driver type	Slotted
Head type	Countersunk
Length / Height, external	25 mm
Material	A2 Stainless Steel
Plating	Unplated
RoHS Compliant	YES
Thread size	M6 x 25