

**SurgeArrest Essential**

APC Essential SurgeArrest 6 Outlet 10 Foot Cord, 120V


P610

Basic Protection for Computers and Electronics

Includes: User Manual

Standard Lead Time: Usually in Stock



Output	
Number of Outlets	6
Receptacle Style	NEMA 5-15R
Input	
Nominal Input Voltage	120V
Input Power	1200 Watts
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P 
Maximum Line Current per phase	15A
Cord Length	3.05 meters
Maximum Input Current	15A
Input Breaker Capacity	15.0 A
Surge Protection and Filtering	
Surge energy rating	1080 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40 dB
Peak Current Normal Mode	60 (/PH) kAmps
Peak Current Common Mode	72 kAmps
NM Surge Response Time (ns)	1 ns
Let Through Voltage Rating	< 500
Physical	
Net Weight	0.59 KG
Maximum Height	286.00 mm
Maximum Width	51.00 mm
Maximum Depth	38.00 mm
Shipping Weight	0.64 KG
Shipping Height	305.00 mm
Shipping Width	140.00 mm
Shipping Depth	46.00 mm
Master Carton Units	6.00
Master Carton Dimensions (Length x Width x Height)	295 x 311 x 150 mm
Master Carton Weight	4.75 KG
SCC Codes	1073130428270 6
Color	Beige

Units per Pallet	864.00
<b>Environmental</b>	
Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95%
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95%
Storage Elevation	0-15000 meters
<b>Conformance</b>	
Regulatory Approvals	ETL
Standard Warranty	Lifetime
UL 1449 TVSS Rating	400V
<b>Sustainable Offer Status</b>	
RoHS	Compliant
REACH	REACH: Contains No SVHCs