

3G HSPA+ USB Adapter MA260

⦿ Features:

- Up to 21Mbps download and 5.76Mbps upload (Network Type: WCDMA)
- Micro SD card slot for up to 32GB of optional storage
- Bundled utility provides quick & hassle-free installation
- Internal antenna, no batteries or cables required
- Fast USB 2.0 connection to notebook/desktop computers
- Take your Broadband connection with you wherever you go
- Supports Windows 7 32/64bit, Vista 32/64bit, Windows XP 32/64bit
- Provides HSPA+/HSUPA/HSDPA/UMTS/GPRS/GSM/EDGE network support



⦿ Description:

TP-LINK's 3G HSPA+ USB Adapter, MA260 allows users to acquire 3G mobile broadband access simply by inserting a standard SIM card into the adapter and plugging it into their laptop or desktop computers. It supports the latest 3G HSPA+ technology, which provides improved data transfer rates. Equipped with its internal antenna, micro SD card slot and SIM card slot, the MA260 is a great choice for users to connect to the Internet in locations that are unable to receive conventional broadband. You can enjoy quick and easy access to email, the Internet or business applications on your laptop while on the go.

⊙ Specifications:

| Hardware Features | |
|-------------------------|---|
| Standards and Protocols | WCDMA Network |
| Interface | USB 2.0 |
| Data Rates | DL: 21Mbps, UL: 5.76 Mbps |
| LED Indicator | Two-color LED provides status information |
| Dimensions (W x D x H) | 3.89 x 1.09 x 0.55 in. (99 x 28 x 14 mm) |
| Antenna Type | Internal antenna |
| GSM Band | 850/900/1800/1900 MHz |
| HSUPA Band | 2100 MHz |
| Micro SD Card Reader | Supports standard Micro SD cards up to 32 GB |
| SIM Slot | Standard 6-Pin SIM card interface |
| Others | |
| Certifications | CE, FCC, RoHS |
| System Requirements | Windows 7/Vista/XP (32/64bits) |
| Environment | Operating Temperature: 0°C~40°C (32°F~104°F) |
| | Storage Temperature: -40°C~70°C (-40°F~158°F) |
| | Operating Humidity: 10%~90% non-condensing |
| | Storage Humidity: 5%~90% non-condensing |

⊙ Diagram:



Package:

- 3G HSPA+ USB Adapter MA260
- Quick Installation Guide

Related Products:

- 3.75G HSUPA USB Adapter MA180
- Portable Battery Powered 3G/4G Wireless N Router TL-MR3040
- 300Mbps 3G/4G Wireless N Router TL-MR3420
- 150Mbps 3G/4G Wireless N Router TL-MR3220