



ROEBUCK TOGGLE CLAMP MG7B

Base mounted

Solid bar with spindle retainer supplied loose for welding in desired position

Supplied with set screw and nuts

Manufactured from zinc plated and passivated steel

Clamping pressure	88 kg
Dimension A	103 mm
Dimension B	40 mm
Dimension C	25.5 mm
Dimension D	64 mm
Dimension E	27 mm
Dimension F	12.5 mm
Dimension G	20 mm
Dimension H	5.5 mm
Dimension I	M6 x 40 mm
Dimension, A	103 mm
Dimension, B	40 mm
Dimension, C	25.5 mm
Dimension, D	64 mm
Dimension, E	27 mm
Dimension, F	12.5 mm

Dimension, G	20 mm
Dimension, H	M6 X 40 mm
Holding pressure	113 kg
RoHS Compliant	NA
Weight	0.20 kg