

## CWMS



### Article number: 592-11109

These weatherproof cotton fabric identification labels can be used either inside or outside. The material's flexibility and thick rubber adhesive ensures good contact is maintained even on uneven substrates. The labels are supplied on handy cards and are easy to remove prior to application.

For the identification of cables, pipes, and connectors. Ideal for on-site installation.



### Base Data

Cable $\varnothing$ min	0 mm
Colour	Yellow (YE)
Marking Text	pen
Mounting method Identification ETIM	Pasting / Stick
Type	CWMS-PEN-260-YE
Variant	Card form
With label space ETIM	Yes

### Product Dimensions

Bundle $\varnothing$ max.	4.0 mm
Bundle $\varnothing$ min.	0.0 mm
Core diameter from / to	4.00 - 4.00 mm
Height (H)	19 mm
Outside $\varnothing$ max.	4 mm
Outside $\varnothing$ min.	0 mm
Thickness (T)	150 $\mu$ m
Thickness of Foil ( $\mu$ m)	150.0 $\mu$ m
Width (W)	6.2 mm

### Logistic and Packaging

Carton Quantity	1
EAN code	4031026172750
Labels per Sheet	72
Pack Cont.	1800
Quantity of Europallet	0 pcs.
Quantity per	Pack
Sheets per Pack	25
Weight (Kg)	0.1 kg

### Material and Specifications

Adhesive	Synthetic rubber
Chem. Material Properties	resistant to oils, water and solvents
Curing Temperature	From +4 °C
Halogenfree	NO
Material	260
Material	260 CWMS
Operating Temperature	-40 °C to +120 °C

