


**Datasheet**

Art.No. 80.063.4032.0

Relay FLARE MOVE 38 24VDC6A

flareMOVE, relay 24VDC, 1 change-over contact, plugable, input voltage 24 V/DC output: 250 V AC / 6 A



Art.No.	80.063.4032.0
EAN	4015573659315
Order unit	10 pieces

**Approvals**

**Technical data**

**General**

Connection type	Plug-in connection
Number of change-over contacts	1
Detachable clamps	No
Drive, polarization	Polarity free
Drive, function	Mono stable
Forced-guided contacts	No
Complete with socket	No
Degree of protection (IP)	IP20

**Technical data**

Type of excitation	
Nominal voltage DC	24 V
Lower nominal voltage DC	24 V
Upper nominal voltage DC	24 V

**Dimensions**

Depth	15 mm
Width	5 mm
Height	28 mm