



NOTES:

4. SAME AS M39012/21-0002, KC-79-106 EXCEPT FOR FINISH.

- UNLESS OTHERWISE SPECIFIED:
- TOLERANCES: FRACTIONS ± .010 DECIMALS ± .004 ANGLES ± 0° 30' T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED THE SUM OF THEIR TOLERANCES.
  - REMOVE ALL BURRS. BREAK SHARP EDGES .003 MAX.
  - NO FILLETS PERMITTED.
  - SURFACE ROUGHNESS 32 MICROINCHES RMS MAX.
  - ALL DIMENSIONS PRIOR TO PLATING.



S-D

KC-79-131

REVISIONS	
ISSUE	CHANGES
0	ER 3072 C.C. 7 DEC 70
1	CN 12479 A JL 28 JUL 75
2	CN 14568 C GA 24 JUN 75
3	CN 19252 C GMF 17 FEB 80
4	CN 21551 C KOR 21 JAN 81

S-D

S-D

ITEM	REQ'D	DESCRIPTION	DWG. NO.
7	1	BNC CONTACT ASSEMBLY	
6	1	HEX NUT	708-4-MOG
5	1	LOCKWASHER	C-71-09-7-MOG
2	1	INSULATOR	
1	1	BODY	

REF.

FINISH

SPEC KER-10004

MATL

SPEC

BNC BULK HEAD RECEPTACLE

DRAWN C.C. DATE 3 DEC 70

APPR JC DATE 12-7-70

KINGS ELECTRONICS  
44 MARLBOROUGH ROAD  
TUCKAHOE, N. Y.

DWG. NO. KC-79-131