

Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

StarLEDs

Bi-Pin - T-1

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: 15015450 



**StarLED, Bi-Pin 2,54 LED-Lamp,
28V AC/DC, red**

Description

Designation: StarLED, Bi-Pin 2,54 LED-Lamp,
28V AC/DC, red

Product range: StarLED

Optical features

Colour: red

Dominant Wavelength: 630 nm

Number of LEDs: 1

Typ. Luminous intensity: 230 mcd (at DC current)

Electrical features

Operating Voltage: 28 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 10 mA

Mechanical features

Socket: Bi-Pin 2,54

Lamp size: T-1

Length: 10 mm

Diameter: 3,8 mm

Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

Gallery

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful
surveillance audit
according to ISO
9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in
CML products
>> [More details](#)



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.

 **Multivoltage LED Lamps**
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket

