



Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

StarLEDs

T5,5k

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: 1504145W3D



StarLED, T5.5k LED-Lamp, 28V AC/DC, cold white

Description

Designation: StarLED, T5.5k LED-Lamp, 28V AC/DC, cold white

Product range: StarLED

Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 1

Typ. Luminous intensity: 350 mcd (at DC current)

LED epoxy type: diffused

Electrical features

Operating Voltage: 28 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 14 mA

Mechanical features

Socket: T5.5k

Length: 22 mm

Lamp size: T5.5k

Diameter: 5,8 mm

Thermal features

Operating temperature: -20...+60 °C

Storage temperature: -25...+80 °C

Gallery

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful surveillance audit according to ISO 9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in CML products
>> [More details](#)



[Standard Image](#)

[Drawing](#)

Click on a small picture to select it. Click the large image to view full size.

 **Multivoltage LED Lamps**
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket

