

Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

Mega StarLEDs

BA9s - 3x3mm LEDs

BA9s, Railway
Application

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: 1862045W3 



**Mega StarLED, BA9s LED-Lamp,
28V AC/DC, cold white**

Description

Designation: Mega StarLED, BA9s LED-Lamp,
28V AC/DC, cold white

Description: Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.

Manufacturer: CML Technologies GmbH & Co. KG

Item status: available

Application: Industry

Product range: Mega StarLED

Optical features

Colour: cold white

Coordinates in colour: 0,31 / 0,32

Number of LEDs: 3

Typ. Luminous intensity: 3 x 2100 mcd (at DC current)

LED epoxy type: clear

Comment: Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

Electrical features

Operating Voltage: 28 V

Voltage type: AC/DC

Rectifier: Half wave

Voltage tolerance: 10 %

DC current: 7 mA

Mechanical features

Socket: BA9s

Material plastic: Makrolon 2805

Length: 25 mm

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful surveillance audit according to ISO 9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in CML products
>> [More details](#)

Lamp size: T-3 1/4
Diameter: 10 mm

Thermal features

Operating temperature: -20...+60 °C
Storage temperature: -25...+80 °C

Gallery



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.



Multivoltage LED Lamps
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket

