



Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

Mega StarLEDs

BA15d - 6x3mm LEDs

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: 1864035W3



Mega StarLED, BA15d LED-Lamp, 24-28V AC/DC, cold white

Description

Designation: Mega StarLED, BA15d LED-Lamp, 24-28V AC/DC, cold white

Description: Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.

Manufacturer: CML Technologies GmbH & Co. KG

Item status: available

Application: Industry

Product range: Mega StarLED

Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 6

Typ. Luminous intensity: 6 x 1800 - 2400 mcd (at DC current)

LED epoxy type: clear

Comment: Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

Electrical features

Operating Voltage: 24-28 V

Voltage type: AC/DC

Rectifier: Bridge

Voltage tolerance: 10 %

Current: 12 - 16 mA

Mechanical features

Socket: BA15d

Material plastic: Makrolon 2805

Latest News

2013-01-08
 LEDS MADE EASY.
 >> [More details](#)

2012-03-09
 Successful surveillance audit according to ISO 9001:2008
 >> [More details](#)

2012-02-24
 Latest Nichia LEDs in CML products
 >> [More details](#)

Lamp size: T-5
Length: 35 mm
Diameter: 16 mm

Thermal features

Operating temperature: -20...+60 °C
Storage temperature: -25...+80 °C

Gallery



[Standard Image](#)

[Drawing](#)



Click on a small picture to select it. Click the large image to view full size.



Multivoltage LED Lamps
Covering the voltage range of 6 to 32V
Available in all colours and BA9s socket

