



Product Search

Item no...

Product Catalog

Products

[Lamps & LED-Lamps](#)

[LED lamps](#)

[Mega StarLEDs](#)

[BA15d - 6x3mm LEDs](#)

Markets

[Automotive](#)

[Aviation](#)

[Gaming](#)

[Illumination](#)

[Transport](#)

[Custom Projects](#)

Product details

Article: 1864035W3D



Mega StarLED, BA15d LED-Lamp, 24-28V AC/DC, cold white

Description

Designation: Mega StarLED, BA15d LED-Lamp, 24-28V AC/DC, cold white

Description: Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.

Manufacturer: CML Technologies GmbH & Co. KG

Item status: available

Application: Industry

Product range: Mega StarLED

Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 6

Typ. Luminous intensity: 6 x 900 - 1200 mcd (at DC current)

LED epoxy type: diffused

Comment: Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

Electrical features

Operating Voltage: 24-28 V

Voltage type: AC/DC

Rectifier: Bridge

Voltage tolerance: 10 %

Current: 12 - 16 mA

Mechanical features

Socket: BA15d

Material plastic: Makrolon 2805

Lamp size: T-5

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful surveillance audit according to ISO 9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in CML products
>> [More details](#)

Length: 35 mm
Diameter: 16 mm

Thermal features

Operating temperature: -20...+60 °C
Storage temperature: -25...+80 °C

Gallery



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.



LED Lamps according EN 50155
Designed for rolling stock applications
Long life time including safety feature

