



Product Search

Item no...

Product Catalog

Products

Lamps & LED-Lamps

LED lamps

Mega StarLEDs

E14 - 6x3mm LEDs

Markets

Automotive

Aviation

Gaming

Illumination

Transport

Custom Projects

Product details

Article: 1864713W3



**Mega StarLED, E14 LED-Lamp,
130V AC/DC, cold white**

Description

Designation: Mega StarLED, E14 LED-Lamp,
130V AC/DC, cold white

Description: Mega StarLEDs are equipped with more than one LED. Consequently, higher brightness and better light distribution can be achieved.

Manufacturer: CML Technologies GmbH & Co. KG

Item status: available

Application: Industry

Product range: Mega StarLED

Optical features

Colour: cold white

Coordinates in colour 0,31 / 0,32

Number of LEDs: 6

Typ. Luminous intensity: 6 x 1200 mcd (at DC current)

LED epoxy type: clear

Comment: Due to manufacturing tolerances of the LEDs may be slight variations in color (color temperature).

Electrical features

Operating Voltage: 130 V

Voltage type: AC/DC

Rectifier: Bridge

Voltage tolerance: 10 %

Current: 4 mA

Mechanical features

Socket: E14

Material plastic: Makrolon 2805

Lamp size: T-5

Latest News

2013-01-08
LEDS MADE EASY.
>> [More details](#)

2012-03-09
Successful surveillance audit according to ISO 9001:2008
>> [More details](#)

2012-02-24
Latest Nichia LEDs in CML products
>> [More details](#)

Length: 35 mm
Diameter: 16 mm

Thermal features

Operating temperature: -20...+60 °C
Storage temperature: -25...+80 °C

Gallery



[Standard Image](#)

[Drawing](#)

[Image](#)

Click on a small picture to select it. Click the large image to view full size.

