



Features & Benefits

- Easy to install
- Suitable for 10-Gigabit Ethernet applications
- High Density 24 ports
- Rear cable management
- Earth connection
- Robust all steel construction

Specification

Width	483mm (19")
Depth	98mm
Height	1u (44.5mm)
Material	Mild steel
Finish	Matt black polyester paint
Socket	High performance side entry RJ45 jacks
Socket Labels	Write-on silk screen on panel front
IDC Labelling	Colour coded to T568B
Conforms to	TIA/EIA-568-C Category 6A Specification

Ordering Information

Product Description	Part Number
CCS Category 6A 2020 24 Way FTP Panel	009-002-001-40

Connectix Category 6A Patch Panels provide exceptional performance for high speed LAN's including 10-Gigabit Ethernet applications. The boards are designed using the latest noise compensation techniques and the shielding feature can minimise the risk of EMI.

The 2020 Series FTP Panel offers Cat 6A performance and has been designed to present the cable termination IDCs horizontally on a tray at the rear of the panel, making termination and cable management easier.

All sockets in the panel are commonly linked through the panel and can be grounded to the rack using the earth wire provided. When combined with Connectix Category 6A FTP Modules and Cable, the link will perform well in excess of Category 6A specifications.

