

Path: [Home](#) > [Enclosure Index](#) > Extruded Aluminum w/ **Plastic** End Panels



(click to enlarge)

**Black Anodized
(Open View)**



(click to enlarge)


**Black Anodized
(Assembled View)**



(click to enlarge)













**Clear Anodized
(Assembled View)**



































































Key Features:







- Designed to house P.C. boards or for equipment interfacing.
- Sized for standard Eurocards.
- P.C. boards mount horizontally by sliding into internal slots extruded into the enclosure body.
- Rugged body constructed from extruded aluminum with a minimum thickness of .06" (1.5 mm).
- Extruded body includes a slide removable "belly" plate - except in smaller "A", "B" and "C" sizes (ie...1455A802, 1455B1202 sizes etc.)
- See  "[photo tables](#)" for more visual details.
- Smaller sizes ("A" & "B") are rounded for better hand held ergonomics.

Includes:

- Two easy to machine, black solid ABS plastic end panels with integral bezel (link here if you prefer our [metal end panel version](#))
- Extruded, anodized aluminum body (choice of either clear or black)
- All hardware - end panel screws are #6 x 3/8" TTT - thread rolling, steel screws with a #4 flat head phillips drive - with black zinc plate finish. For replacement screws (quantity 100) order part number **1455MS100BK**
- Self adhesive rubber feet
- **NOTE:** Recommended screw torque is 5 lbf/in

Part Number	Aluminum Anodized Color	PDF Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	Units	Length	Width	Height
1455D602 1455D602BK	Clear	 196K	 163K	 162K	Inches	2.36	1.76	0.99
	Black				mm	60	45	25
1455D802 1455D802BK	Clear	 192K	 164K	 162K	Inches	3.15	1.76	0.99
	Black				mm	80	45	25
1455A802 1455A802BK	Clear	 109K	 125K	 121K	Inches	3.15	2.76	0.47
	Black				mm	80	70	12
1455B802 1455B802BK	Clear	 215K	 151K	 157K	Inches	3.15	2.82	0.75
	Black				mm	80	71.7	19

1455C802 1455C802BK	Clear				Inches	3.15	2.13	0.91
	Black	220K	134K	111K	mm	80	54	23
1455A1002 1455A1002BK	Clear				Inches	3.94	2.76	0.47
	Black	209K	122K	121K	mm	100	70	12
1455B1002 1455B1002BK	Clear				Inches	3.94	2.82	0.75
	Black	204K	151K	157K	mm	100	71.7	19
1455A1202 1455A1202BK	Clear				Inches	4.72	2.76	0.47
	Black	203K	122K	121K	mm	120	70	12
1455B1202 1455B1202BK	Clear				Inches	4.72	2.82	0.75
	Black	215K	150K	157K	mm	120	71.7	19
1455C1202 1455C1202BK	Clear				Inches	4.72	2.13	0.91
	Black	216K	130K	111K	mm	120	54	23
1455J1202 1455J1202BK	Clear				Inches	4.72	3.07	1.06
	Black	249K	145K	203K	mm	120	78	27
1455K1202 1455K1202BK	Clear				Inches	4.72	3.07	1.69
	Black	345K	152K	212K	mm	120	78	43
1455L1202 1455L1202BK	Clear				Inches	4.72	4.06	1.20
	Black	264K	149K	206K	mm	120	103	30.5
1455N1202 1455N1202BK	Clear				Inches	4.72	4.06	2.09
	Black	258K	149K	226K	mm	120	103	53
1455J1602 1455J1602BK	Clear				Inches	6.30	3.07	1.06
	Black	255K	156K	203K	mm	160	78	27
1455K1602 1455K1602BK	Clear				Inches	6.30	3.07	1.69
	Black	245K	152K	212K	mm	160	78	43
1455L1602 1455L1602BK	Clear				Inches	6.30	4.06	1.20
	Black	264K	148K	206K	mm	160	103	30.5
1455N1602 1455N1602BK	Clear				Inches	6.30	4.06	2.09
	Black	244K	168K	227K	mm	160	103	53
1455P1602 1455P1602BK	Clear				Inches	6.30	4.92	1.20
	Black	261K	147K	215K	mm	160	125	30.5
1455Q1602 1455Q1602BK	Clear				Inches	6.30	4.92	2.03
	Black	279K	153K	256K	mm	160	125	51.5
1455R1602 1455R1602BK	Clear				Inches	6.30	6.50	1.2
	Black	162K	123K	288K	mm	160	165	30.5
1455T1602 1455T1602BK	Clear				Inches	6.30	6.50	2.1
	Black	163K	125K	256K	mm	160	165	51.5
1455L2202 1455L2202BK	Clear				Inches	8.66	4.06	1.20
	Black	269K	150K	206K	mm	220	103	30.5
1455N2202 1455N2202BK	Clear				Inches	8.66	4.06	2.09
	Black	247K	148K	227K	mm	220	103	53
1455P2202 1455P2202BK	Clear				Inches	8.66	4.92	1.20
	Black	250K	148K	215K	mm	220	125	30.5
1455Q2202 1455Q2202BK	Clear				Inches	8.66	4.92	2.03
	Black	375K	155K	256K	mm	220	125	51.5

1455R2202 1455R2202BK	Clear				Inches	8.66	6.50	1.2
	Black	149K	124K	288K	mm	220	165	30.5
1455T2202 1455T2202BK	Clear				Inches	8.66	6.50	2.1
	Black	166K	128K	256K	mm	220	165	51.5

 [Link here to photo tables](#) of each part number

Accessories

Wallmount Options:












(click to enlarge)



(click to enlarge)

- Designed to convert these enclosures where shelf or wall mounting is required
- Flanges are .064" (1.6 mm) thick aluminum foot "L" brackets and attach to each end, replacing the plastic end panels
- Finish available in both clear & black anodized to match enclosure
- **SOLD IN PAIRS**

Part Number	Color	 Reader File	AutoCAD .dwg Files (zipped)	3D Solid Model .igs & .stp files (zipped)	USE WITH ENCLOSURE
1455CF 1455CFBK	Clear Black	 142K	 94K	 24K	Any part above starting with 1455C
1455JF 1455JFBK	Clear Black	 174K	 83K	 25K	Any part above starting with 1455J
1455KF 1455KFBK	Clear Black	 159K	 118K	 23K	Any part above starting with 1455K
1455LF 1455LFBK	Clear Black	 160K	 110K	 25K	Any part above starting with 1455L
1455NF 1455NFBK	Clear Black	 165K	 111K	 25K	Any part above starting with 1455N
1455PF 1455PFBK	Clear Black	 180K	 112K	 87K	Any part above starting with 1455P
1455QF 1455QFBK	Clear Black	 145K	 113K	 25K	Any part above starting with 1455Q
1455RF 1455RFBK	Clear Black	 143K	 111K	 25K	Any part above starting with 1455R
1455TF 1455TFBK	Clear Black	 150K	 111K	 25K	Any part above starting with 1455T

Replacement Parts & Bezel Options:



(click to enlarge)

Black Plastic - Solid Bezel

USE WITH (Enclosure Part Number)	Black Plastic Solid Bezel	
	(2 Pack)	(10 Pack)
1455D602	1455DPLBK	1455DPLBK-10
1455D802	1455DPLBK	1455DPLBK-10
1455A802	1455APLBK	1455APLBK-10
1455A1202	1455APLBK	1455APLBK-10
1455B802	1455BPLBK	1455BPLBK-10
1455B1202	1455BPLBK	1455BPLBK-10
1455C802	1455CPLBK	1455CPLBK-10
1455C1202	1455CPLBK	1455CPLBK-10
1455J1202	1455JPLBK	1455JPLBK-10
1455K1202	1455KPLBK	1455KPLBK-10
1455L1202	1455LPLBK	1455LPLBK-10
1455N1202	1455NPLBK	1455NPLBK-10
1455J1602	1455JPLBK	1455JPLBK-10
1455K1602	1455KPLBK	1455KPLBK-10
1455L1602	1455LPLBK	1455LPLBK-10
1455N1602	1455NPLBK	1455NPLBK-10
1455P1602	1455PPLBK	1455PPLBK-10
1455Q1602	1455QPLBK	1455QPLBK-10
1455R1602	1455RPLBK	1455RPLBK-10
1455T1602	1455TPLBK	1455TPLBK-10
1455L2202	1455LPLBK	1455LPLBK-10
1455N2202	1455NPLBK	1455NPLBK-10
1455P2202	1455PPLBK	1455PPLBK-10
1455Q2202	1455QPLBK	1455QPLBK-10
1455R2202	1455RPLBK	1455RPLBK-10
1455T2202	1455TPLBK	1455TPLBK-10



(click to enlarge)



(click to enlarge)

Red ABS Plastic - Solid Bezel

Yellow ABS Plastic - Solid Bezel

USE WITH (Enclosure Part Number)	Red		Yellow	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C802	1455CPLRED	1455CPLRED-10	1455CPLY	1455CPLY-10
1455C1202	1455CPLRED	1455CPLRED-10	1455CPLY	1455CPLY-10
1455J1202	1455JPLRED	1455JPLRED-10	1455JPLY	1455JPLY-10
1455K1202	1455KPLRED	1455KPLRED-10	1455KPLY	1455KPLY-10
1455L1202	1455LPLRED	1455LPLRED-10	1455LPLY	1455LPLY-10
1455N1202	1455NPLRED	1455NPLRED-10	1455NPLY	1455NPLY-10
1455J1602	1455JPLRED	1455JPLRED-10	1455JPLY	1455JPLY-10
1455K1602	1455KPLRED	1455KPLRED-10	1455KPLY	1455KPLY-10
1455L1602	1455LPLRED	1455LPLRED-10	1455LPLY	1455LPLY-10
1455N1602	1455NPLRED	1455NPLRED-10	1455NPLY	1455NPLY-10
1455P1602	1455PPLRED	1455PPLRED-10	1455PPLY	1455PPLY-10
1455Q1602	1455QPLRED	1455QPLRED-10	1455QPLY	1455QPLY-10
1455R1602	1455RPLRED	1455RPLRED-10	1455RPLY	1455RPLY-10
1455T1602	1455TPLRED	1455TPLRED-10	1455TPLY	1455TPLY-10
1455L2202	1455LPLRED	1455LPLRED-10	1455LPLY	1455LPLY-10
1455N2202	1455NPLRED	1455NPLRED-10	1455NPLY	1455NPLY-10
1455P2202	1455PPLRED	1455PPLRED-10	1455PPLY	1455PPLY-10
1455Q2202	1455QPLRED	1455QPLRED-10	1455QPLY	1455QPLY-10
1455R2202	1455RPLRED	1455RPLRED-10	1455RPLY	1455RPLY-10
1455T2202	1455TPLRED	1455TPLRED-10	1455TPLY	1455TPLY-10



(click to enlarge)



(click to enlarge)



(click to enlarge)
Translucent Blue
Polycarbonate - Solid Bezel

(click to enlarge)
Translucent (IR) Red
Polycarbonate - Solid Bezel

USE WITH (Enclosure Part Number)	Translucent Blue		Translucent Red	
	(2 Pack)	(10 Pack)	(2 Pack)	(10 Pack)
1455C802	1455CPLTBU	1455CPLTBU-10	1455CPLTRD	1455CPLTRD-10
1455C1202	1455CPLTBU	1455CPLTBU-10	1455CPLTRD	1455CPLTRD-10
1455J1202	1455JPLTBU	1455JPLTBU-10	1455JPLTRD	1455JPLTRD-10
1455K1202	1455KPLTBU	1455KPLTBU-10	1455KPLTRD	1455KPLTRD-10
1455L1202	1455LPLTBU	1455LPLTBU-10	1455LPLTRD	1455LPLTRD-10
1455N1202	1455NPLTBU	1455NPLTBU-10	1455NPLTRD	1455NPLTRD-10
1455J1602	1455JPLTBU	1455JPLTBU-10	1455JPLTRD	1455JPLTRD-10
1455K1602	1455KPLTBU	1455KPLTBU-10	1455KPLTRD	1455KPLTRD-10
1455L1602	1455LPLTBU	1455LPLTBU-10	1455LPLTRD	1455LPLTRD-10
1455N1602	1455NPLTBU	1455NPLTBU-10	1455NPLTRD	1455NPLTRD-10
1455P1602	1455PPLTBU	1455PPLTBU-10	1455PPLTRD	1455PPLTRD-10
1455Q1602	1455QPLTBU	1455QPLTBU-10	1455QPLTRD	1455QPLTRD-10
1455R1602	1455RPLTBU	1455RPLTBU-10	1455RPLTRD	1455RPLTRD-10
1455T1602	1455TPLTBU	1455TPLTBU-10	1455TPLTRD	1455TPLTRD-10
1455L2202	1455LPLTBU	1455LPLTBU-10	1455LPLTRD	1455LPLTRD-10
1455N2202	1455NPLTBU	1455NPLTBU-10	1455NPLTRD	1455NPLTRD-10
1455P2202	1455PPLTBU	1455PPLTBU-10	1455PPLTRD	1455PPLTRD-10
1455Q2202	1455QPLTBU	1455QPLTBU-10	1455QPLTRD	1455QPLTRD-10
1455R2202	1455RPLTBU	1455RPLTBU-10	1455RPLTRD	1455RPLTRD-10
1455T2202	1455TPLTBU	1455TPLTBU-10	1455TPLTRD	1455TPLTRD-10



NOW catalog pages on this series (193K) [9C-1455.pdf](#)

Exactly what you are looking for???
 Link to our stocking distributors - most have "on-line" pricing, stock check and ordering!!!

Our Distributors

[Order from your favorite distributor](#)

[Home](#) | [Products](#) | [Distributors](#) | [Technical](#) | [Contact Us](#) | [Other Options](#)