

**FEX FEX 3819 13 T**



Sample photo

**Order symbol:** FEX 3819 13 T  
**Product nbr:** 4120802  
**Description:** Enclosure, PC  
**Remarks:** Ex e II, EN 60079; IK 4J

**EAN:** 6418074007940  
**El. number:**  
 Finland: 3424650  
 Denmark: 8212026434  
 Italy: 7801030  
 Sweden: 4120802  
 Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with silicone gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		378	188	130	Ingress Protection (EN 60529): IP 54
<b>inch:</b>		14.9	7.4	5.1	Impact Resistance (EN 50014): 4J
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Base colour:</b>		RAL 7035			<b>Certificates:</b> ATEX EC Certificate of Conformity
<b>Cover colour:</b>		Clear transparent			
<b>Cover screws material:</b>		Polyamide			
<b>Cover screws colour:</b>		Grey			
<b>Gasket material:</b>		Silicone			
<b>Temperatures:</b>					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-10 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		14 ... 175 °F			
<b>Accessories:</b>					
EKHVT		Mounting plate			
EKJVT		Mounting plate			
EKMVT		Mounting plate			
EKOVT		Mounting plate			
EKPVT		Mounting plate			
EKTVT		Mounting plate			
EKUVT		Mounting plate			
EKV 12		DIN-35 Mounting rail			
EKV 22		DIN-35 Mounting rail			
EKV 32		DIN-35 Mounting rail			

