

Order symbol: ALX 061505
Product nbr: 7015100
Description: Enclosure, aluminium
Remarks: II 2GD; Ex e IIC Gb; Ex tb IIIC Db IP66

EAN: 6418074009340
El. number:
 Finland: 3421807
 Denmark: 8212026573
 Sweden: 7015100
 Norway:

Including: Base, cover with silicone/PUR gasket, stainless steel cover screws, with mounting and earth screws and earth terminal.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		152	66	46	ARM 0818	DIN-15 Mounting rail
inch:		6.0	2.6	1.8	ARM 0825	DIN-15 Mounting rail
Materials:						
Material:	Aluminium					
Base colour:	RAL 7001					
Cover colour:	RAL 7001					
Cover screws material:	Stainless steel					
Gasket material:	Silicone					
Temperatures:						
Short term:	PUR -40 / Si -50 ... 80 °C					
Continuous:	PUR -40 / Si -50 ... 80 °C					
Short term:	PUR -40 / Si -58 ... 175 °F					
Continuous:	PUR -40 / Si -58 ... 175 °F					
Accessories:						
AM 0808	Mounting plate					
AM 0813	Mounting plate					
AM 0818	Mounting plate					
AM 0825	Mounting plate					
AM 1212	Mounting plate					
AM 1222	Mounting plate					
AM 1236	Mounting plate					
AM 1616	Mounting plate					
AM 1626	Mounting plate					
ARM 0610	DIN-15 Mounting rail					
ARM 0615	DIN-15 Mounting rail					
ARM 0808	DIN-15 Mounting rail					
ARM 0813	DIN-15 Mounting rail					
Rating:						
Ingress Protection (EN 60529): IP 66						
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13						
Certificates:						
ATEX						
EC Certificate of Conformity						

