

ALX ALX 081806



Sample photo

Order symbol: ALX 081806
Product nbr: 7015170
Description: Enclosure, aluminium
Remarks: II 2GD; Ex e IIC Gb; Ex tb IIIC Db IP66

EAN: 6418074009371
El. number:
 Finland: 3421813
 Denmark: 8212026609
 Sweden: 7015170
 Norway:

Including: Base, cover with silicone/PUR gasket, stainless steel cover screws, with mounting and earth screws and earth terminal.

Dimensions:		Length	Width	Height	Accessories:	
mm:		177	81	57	ARM 0818	DIN-15 Mounting rail
inch:		7.0	3.2	2.2	ARM 0825	DIN-15 Mounting rail
Materials:						
Material:		Aluminium		ARH 12	DIN-35 Mounting rail	
Base colour:		RAL 7001		ARH 16	DIN-35 Mounting rail	
Cover colour:		RAL 7001		ARH 22	DIN-35 Mounting rail	
Cover screws material:		Stainless steel		ARH 26	DIN-35 Mounting rail	
Gasket material:		Silicone/PUR		ARH 36	DIN-35 Mounting rail	
Temperatures:						
Short term:		PUR -40 / Si -50 ... 80 °C		MRS 28540	Wall fastening lug (2 pcs)	
Continuous:		PUR -40 / Si -50 ... 80 °C		MRS 28541	Wall fastening lug (2 pcs)	
Short term:		PUR -40 / Si -58 ... 175 °F		Rating:		
Continuous:		PUR -40 / Si -58 ... 175 °F		Ingress Protection (EN 60529): IP 66		
Accessories:						
AM 0808		Mounting plate		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
AM 0813		Mounting plate		Certificates:		
AM 0818		Mounting plate		ATEX		
AM 0825		Mounting plate		EC Certificate of Conformity		
AM 1212		Mounting plate				
AM 1222		Mounting plate				
AM 1236		Mounting plate				
AM 1616		Mounting plate				
AM 1626		Mounting plate				
ARM 0610		DIN-15 Mounting rail				
ARM 0615		DIN-15 Mounting rail				
ARM 0808		DIN-15 Mounting rail				
ARM 0813		DIN-15 Mounting rail				

