

**ALX ALX 121208**



Sample photo

**Order symbol:** ALX 121208  
**Product nbr:** 7015210  
**Description:** Enclosure, aluminium  
**Remarks:** II 2GD; Ex e IIC Gb; Ex tb IIIC  
 Db IP66

**EAN:** 6418074009395  
**El. number:**  
 Finland: 3421817  
 Denmark: 8212026625  
 Sweden: 7015210  
 Norway:

Including: Base, cover with PUR gasket, stainless steel cover screws, with mounting and earth screws and earth terminal.

Dimensions:		Length	Width	Height	Accessories:	
<b>mm:</b>		125	124	81	ARM 0818	DIN-15 Mounting rail
<b>inch:</b>		4.9	4.9	3.2	ARM 0825	DIN-15 Mounting rail
<b>Materials:</b>						
<b>Material:</b>		Aluminium		ARH 12	DIN-35 Mounting rail	
<b>Base colour:</b>		RAL 7001		ARH 16	DIN-35 Mounting rail	
<b>Cover colour:</b>		RAL 7001		ARH 22	DIN-35 Mounting rail	
<b>Cover screws material:</b>		Stainless steel		ARH 26	DIN-35 Mounting rail	
<b>Gasket material:</b>		Polyurethane		ARH 36	DIN-35 Mounting rail	
<b>Temperatures:</b>						
<b>Short term:</b>		PUR -40 / Si -50 ... 80 °C		MRS 28540	Wall fastening lug (2 pcs)	
<b>Continuous:</b>		PUR -40 / Si -50 ... 80 °C		MRS 28541	Wall fastening lug (2 pcs)	
<b>Short term:</b>		PUR -40 / Si -58 ... 175 °F		<b>Rating:</b>		
<b>Continuous:</b>		PUR -40 / Si -58 ... 175 °F		Ingress Protection (EN 60529): IP 66		
<b>Accessories:</b>						
AM 0808		Mounting plate		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
AM 0813		Mounting plate		<b>Certificates:</b>		
AM 0818		Mounting plate		ATEX		
AM 0825		Mounting plate		EC Certificate of Conformity		
AM 1212		Mounting plate				
AM 1222		Mounting plate				
AM 1236		Mounting plate				
AM 1616		Mounting plate				
AM 1626		Mounting plate				
ARM 0610		DIN-15 Mounting rail				
ARM 0615		DIN-15 Mounting rail				
ARM 0808		DIN-15 Mounting rail				
ARM 0813		DIN-15 Mounting rail				

