

CAB CAB ABS 303018 G



Sample photo

Order symbol: CAB ABS 303018 G
Product nbr: 8183340
Description: Cabinet, ABS, Grey door
Remarks: Latches on the long side

EAN: 6418074020161
El. number:
 Finland: 3424307
 Denmark: 8212020524
 Italy: 7811025
 Sweden: 2540067
 Norway:

Including: Cabinet base, door with EPDM gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		300	300	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	11.8	7.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		ABS			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			Flammability Rating (UL 746 C 5): UL 94 HB
Cover colour:		RAL 7035			Glow Wire Test (IEC 695-2-1) °C: 650
Gasket material:		EPDM			NEMA Class: NEMA 1, 4, 4X, 12, 13
Temperatures:					Certificates:
Short term:		-40 ... 80 °C			Fimko
Continuous:		-40 ... 60 °C			Europe EN 62208: 2003
Short term:		-40 ... 175 °F			Gost R
Continuous:		-40 ... 140 °F			
Accessories:					
EKIV 33		Mounting plate			
EKIV 27		DIN-35 Mounting rail			
DS35270E1		DIN-35 Mounting rail			
FP A 33		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 33		Front plate			
FP 12-33		Front plate			
FP 12x2-33		Front plate			
DRF 33		DIN rail frame set			

