

CAB CAB PC 302018 G3B



Sample photo

Order symbol: CAB PC 302018 G3B
Product nbr: 8113332
Description: Cabinet, PC, Grey door
Remarks: Lock on the long side

EAN: 6418074020048
El. number:
 Finland: 3424105
 Denmark: 8212019205
 Italy: 7821020
 Sweden: 2539965
 Norway:

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:		Length	Width	Height	Rating:
mm:		300	200	180	Ingress Protection (EN 60529): IP 65
inch:		11.8	7.9	7.1	Impact Resistance (EN 62262): IK 08
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		EPDM			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
EKIV 23		Mounting plate			
EKIV 17		DIN-35 Mounting rail			
DS35170E1		DIN-35 Mounting rail			
EKIV 27		DIN-35 Mounting rail			
DS35270E1		DIN-35 Mounting rail			
FP A 23		Swing-out door/Front plate			
MB 12225 AL		Swing door set			
FP 23		Front plate			
FP 12-23		Front plate			
DRF 23		DIN rail frame set			
Certificates:					
		Germanischer Lloyd (GL)			
		Underwriters Laboratories			
		Fimko			
		Lloyds Register of Shipping (LR)			
		Europe EN 62208: 2003			
		UL Canada			
		Gost R			

