

**CARDMASTER PC 30/25-3**



**Order symbol:** PC 30/25-3  
**Product nbr:** 7525019  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent hinged cover

**EAN:** 6418074056740  
**El. number:**  
 Finland: 3438233  
 Denmark: 8212016677  
 Sweden: 2537308  
 Norway: 2536927

Including: Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		320	260	129	Ingress Protection (EN 60529): IP 65
<b>inch:</b>		12.6	10.2	5.1	Impact Resistance (EN 62262): IK 08/07
<b>Materials:</b>					
<b>Material:</b>		Polycarbonate			Electrical insulation: Totally insulated
<b>Base colour:</b>		RAL 7035			Halogen free (DIN/VDE 0472, Part 815): Yes
<b>Cover colour:</b>		Smoked grey			UV resistance: UL 508
<b>Gasket material:</b>		EPDM and Polyurethane			Flammability Rating (UL 746 C 5): UL 746C 5V
<b>Temperatures:</b>					
<b>Short term:</b>		-40 ... 120 °C			Glow Wire Test (IEC 695-2-1) °C: 960
<b>Continuous:</b>		-40 ... 80 °C			NEMA Class: NEMA 1, 3, 3R, 12, 13
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
<b>Accessories:</b>					
MP 30/25		Mounting plate			
FP 30/25		Front plate (aluminium)			
FC PC 30/25		Frame of PC front plate			
<b>Certificates:</b>					
Underwriters Laboratories					
Fimko					
Europe EN 62208: 2003					
UL Canada					
Gost R					

