



Sample photo

Order symbol: PCM 100/100 G
Product nbr: 6016303
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074038012
El. number:
Finland: 3421632
Denmark: 8212027022
Italy: 7341015
Sweden: 2535306
Norway: 2535505

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		130	80	100	Ingress Protection (EN 60529): IP 66/67
inch:		5.1	3.1	3.9	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		NEMA Class: NEMA 1, 4, 4X, 6	
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Germanischer Lloyd (GL)	
Continuous:		-40 ... 80 °C		Underwriters Laboratories	
Short term:		-40 ... 250 °F		Det Norske Veritas	
Continuous:		-40 ... 175 °F		Fimko	
Accessories:					Europe EN 62208: 2003
MIV 100		Mounting plate (Galvanized steel)		UL Canada	
MIN 5		DIN-15 Mounting rail		Gost R	
MIN 10		DIN-15 Mounting rail			
MIV 5		DIN-35 Mounting rail			
MIV 10		DIN-35 Mounting rail			
FP A 100/130		Front plate (Aluminium)			
HFP 130		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			

