

**MNX PCM 200/150 G**



Sample photo

**Order symbol:** PCM 200/150 G  
**Product nbr:** 6016329  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038166  
**El. number:**  
Finland: 3421654  
Denmark: 8212027381  
Italy: 7341080  
Sweden: 2535351  
Norway: 2535537

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
<b>mm:</b>		255	180	150	Ingress Protection (EN 60529): IP 66/67
<b>inch:</b>		10.0	7.1	5.9	Impact Resistance (EN 62262): IK 08
<b>Materials:</b>					Electrical insulation: Totally insulated
<b>Material:</b>		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
<b>Base colour:</b>		RAL 7035		UV resistance: UL 508	
<b>Cover colour:</b>		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
<b>Cover screws material:</b>		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
<b>Cover screws colour:</b>		Grey		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
<b>Gasket material:</b>		TPE			
<b>Temperatures:</b>					<b>Certificates:</b>
<b>Short term:</b>		-40 ... 120 °C		Germanischer Lloyd (GL)	
<b>Continuous:</b>		-40 ... 80 °C		Underwriters Laboratories	
<b>Short term:</b>		-40 ... 250 °F		Det Norske Veritas	
<b>Continuous:</b>		-40 ... 175 °F		Fimko	
<b>Accessories:</b>					Europe EN 62208: 2003
MIV 200		Mounting plate (Galvanized steel)		UL Canada	
MIN 15		DIN-15 Mounting rail		Gost R	
MIN 20		DIN-15 Mounting rail			
MIV 15		DIN-35 Mounting rail			
MIV 20		DIN-35 Mounting rail			
FP A 200/180		Front plate (Aluminium)			
HFP 180		Front plate hinge series			
FP 22046		Wall fastening lug (4 pcs)			

