

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19216-0003

Status:

Active

Overview:

Splice

Description:

Multi-Lock Connector for 14-16 AWG Wire



image - Reference only

Series

Documents:

- Drawing (PDF)

Product Specification PS-19902-013 (PDF)
- Product Specification PS-19902-011 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Comments

Crimp Quality Equipment

Mil-Spec

MolexKits

Overview

Product Name

UPC

Splices

19216

13.97 x 9.53mm when closed

Yes

N/A

Yes

Splice

Multi-Lock

800753056138

Physical

Barrel Type

Flammability

Insulation

Net Weight

Packaging Type

Temperature Range - Operating

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Closed

94V-0

Polypropylene

1.333/g

Bag

105°C

3.30mm & 4.32mm

14, 16

N/A

Electrical

Voltage - Maximum

600V

Material Info

Old Part Number

ML-1614

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011, PS-19902-013

SD-19216-003

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

19216Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION