

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [09-50-7051](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 3.96mm Pitch KK® Crimp Terminal Housing, 5 Circuits

Documents:

3D Model	Packaging Specification PK-2139-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	2139
Application	Power, Wire-to-Board
MolexKits	Yes
Overview	KK® Interconnection System
Product Name	KK®
UPC	800753531512

Physical

Circuits (maximum)	5
Color - Resin	Natural
Flammability	94V-2
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Net Weight	1.280/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Temperature Range - Operating	See Product Specification

Material Info

Old Part Number	2139-5C
-----------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-2139-001
Product Specification	PS-08-50
Sales Drawing	SD-2139



image - Reference only

Series

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[2139Series](#)

Use With

[2478 Crimp Terminals for 18-24 AWG](#), [2578
Crimp Terminals for 22-26 AWG](#)