


|                   |                            |  |
|-------------------|----------------------------|--|
| U.I. Lapp<br>GmbH | <b>PRODUCT INFORMATION</b> |  |
|                   | <b>SKINTOP® GMP-GL-M</b>   | 12.09.2012   |

Glass fibre-reinforced for maximum mechanical stability  
Supporting surface for spanner means scratches on the housing are avoided



### Application range

For locking SKINTOP® cable glands in boreholes without thread.

### Design

Metric connection thread acc. to EN 50262

### Approvals (Norm references)

UL File Nr. E79903

### Note

UL approval only when used with the UL-approved SKINTOP® polyamide cable glands  
Designed for use with metric SKINTOP® plastic cable glands

### Remark

Photographs are not to scale and do not represent detailed images of the respective products.

### Technical Data


|                    |   |
|--------------------|---|
| On request:        | Available without collar<br>(without surface for assembling tool)                 |
| Colour delivered:  | Silver grey (RAL 7001)<br>Light grey (RAL 7035)<br>Black (RAL 9005), UV-resistant |
| Material:          | Polyamide, glass fibre-reinforced   |
| Temperature range: | Fixed: -40°C to +100°C<br>Dynamic: -20°C to +100°C                                |

|                    |                             |       |
|--------------------|-----------------------------|-------|
| Product Management | Document: LAPP_PRO998EN.pdf | 1 / 3 |
|--------------------|-----------------------------|-------|

**SKINTOP® GMP-GL-M**

12.09.2012

| Part number                          | Article designation / size | SW (mm) | Pieces / PU |
|--------------------------------------|----------------------------|---------|-------------|
| <b>SKINTOP® GMP-GL-M silver grey</b> |                            |         |             |
| 53119000                             | 12 x 1,5                   | 17      | 100         |
| 53119010                             | 16 x 1,5                   | 22      | 100         |
| 53119020                             | 20 x 1,5                   | 27      | 100         |
| 53119030                             | 25 x 1,5                   | 34      | 100         |
| 53119040                             | 32 x 1,5                   | 41      | 100         |
| 53119050                             | 40 x 1,5                   | 50      | 25          |
| 53119060                             | 50 x 1,5                   | 60      | 25          |
| 53119070                             | 63 x 1,5                   | 75      | 25          |
| <b>SKINTOP® GMP-GL-M black</b>       |                            |         |             |
| 53119100                             | 12 x 1,5                   | 17      | 100         |
| 53119110                             | 16 x 1,5                   | 22      | 100         |
| 53119120                             | 20 x 1,5                   | 27      | 100         |
| 53119130                             | 25 x 1,5                   | 34      | 100         |
| 53119140                             | 32 x 1,5                   | 41      | 100         |
| 53119150                             | 40 x 1,5                   | 50      | 25          |
| 53119160                             | 50 x 1,5                   | 60      | 25          |
| 53119170                             | 63 x 1,5                   | 75      | 25          |
| <b>SKINTOP® GMP-GL-M light grey</b>  |                            |         |             |
| 53119003                             | 12 x 1,5                   | 17      | 100         |
| 53119013                             | 16 x 1,5                   | 22      | 100         |
| 53119023                             | 20 x 1,5                   | 27      | 100         |
| 53119033                             | 25 x 1,5                   | 34      | 100         |
| 53119043                             | 32 x 1,5                   | 41      | 100         |
| 53119053                             | 40 x 1,5                   | 50      | 25          |
| 53119063                             | 50 x 1,5                   | 60      | 25          |
| 53119073                             | 63 x 1,5                   | 75      | 25          |

|                   |                            |  |
|-------------------|----------------------------|--|
| U.I. Lapp<br>GmbH | <b>PRODUCT INFORMATION</b> |  <b>LAPP GROUP</b> |
|                   | <b>SKINTOP® GMP-GL-M</b>   | 12.09.2012   |



|                    |                             |       |
|--------------------|-----------------------------|-------|
| Product Management | Document: LAPP_PRO998EN.pdf | 3 / 3 |
|--------------------|-----------------------------|-------|