


Performance and Simplicity at the Best Price!



- ✓ 2 adjustable outputs (0-30 V) and 1 selectable fixed output (2.5 V / 3.3 V / 5 V)
- ✓ Bright 3-digit colour display of currents and voltages simultaneously
- ✓ Simpler use thanks to cordless series or parallel connection
- ✓ Faster work with 4 stored configurations available for recall on front panel
- ✓ High stability and low drift over time in all modes
- ✓ Protection against overvoltages, heating and short-circuits
- ✓ Ventilator control according to power output
- ✓ USB communication

AX 1360-P Programmable Controlled Power Supply

Programmable controlled power supplies are widely used in Research and Development and Test laboratories, electrical and electronic product manufacturing, education, etc.

The AX 1360-P is simple to use, allowing you to change from series to parallel connection by simple selection, without moving any leads. The power supply then switches automatically between the 2 modes.

TECHNICAL SPECIFICATIONS		AX 1360-P	
Number of outputs		3	
VOLTAGE CONTROL			
Output 1		0 – 30 V	
Output 2		0 – 30 V	
Output 3		2.5 V / 3.3 V / 5 V	
CURRENT CONTROL		INDEPENDENT	PARALLEL
Output 1		5 A	6 A
Output 2		5 A	10 A
Output 3		3 A	-
ACCURACY			
Voltage		±(0.5 % reading + 2 digits)	
Current		±(0.5 % reading + 5 digits)	
RESOLUTION			
Voltage		10 mV (0 to 9.99 V) – 100 mV (10 to 30 V)	
Current		10 mA	
RIPPLE AND NOISE			
Voltage		< 1 mV RMS	
TEMPERATURE COEFFICIENT			
Voltage		< 300 ppm/°C	
ON-LOAD		INDEPENDENT AND PARALLEL	
Voltage control		< 0.1 % + 5 mV	
Current control		< 0.2 % + 3 mA	
PROTECTION			
Short-circuits		Current limitation and visual indicated by red LED	
Overcurrent		Fuse	
“SAVE/RECALL” FUNCTION			
No. of stored configurations		4	
TECHNICAL SPECIFICATIONS			
Display		Digital with LEDs – Simultaneous voltage and current in colour	
Current and voltage adjustment		Output 1 and 2 by potentiometers, Output 3 by switch	
Interface / Software		USB / Drivers LV and LW	
Mains power source		220 V / 50 Hz – 60 Hz	
Safety / Protection		IEC 61010-1 / Fuse	
Mechanical specifications		Dimensions: 310 x 250 x 150 mm – Weight: 7.5 kg	
Warranty		1 year	

State at Delivery

AX1360-P : 1 programmable power supply, 1 power cable, 1 USB cable, software on CD Rom and an Operating Manual.

Reference to order: **AX1360-P**



FRANCE
Chauvin Arnoux
 190, rue Championnet
 75876 PARIS Cedex 18
 Tel: +33 1 44 85 44 38
 Fax: +33 1 46 27 95 59
 export@chauvin-arnoux.fr
 www.chauvin-arnoux.fr

UNITED KINGDOM
Chauvin Arnoux Ltd
 Nelson Ct, Flagship Sq, Shaw Cross Business Pk
 Dewsbury, West Yorkshire - WF12 7TH
 Tel: +44 1924 460 494
 Fax: +44 1924 455 328
 info@chauvin-arnoux.co.uk
 www.chauvin-arnoux.com

MIDDLE EAST
Chauvin Arnoux Middle East
 P.O. BOX 60-154
 1241 2020 JAL EL DIB - LEBANON
 Tel: +961 1 890 425
 Fax: +961 1 890 424
 camie@chauvin-arnoux.com
 www.chauvin-arnoux.com

For assistance and ordering