

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-50-0107](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 3.96mm Pitch KK® Crimp Terminal 2578, 22-26 AWG, Reel, Brass, Tin (Sn)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-08-50 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2578
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnection System
Packaging Alternative	08-50-0108 (Loose)
Product Name	KK®
UPC	800753759664

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.150/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A

Material Info

Old Part Number 2578-(P909)

Reference - Drawing Numbers

Product Specification	PS-08-50
Sales Drawing	SD-2578



image - Reference only

EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2578Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 , 5265 , 5239

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030016
Mini-Mac™ Applicator	0638881000
Terminator Die	0011402097
Terminator Die	0011402099
Hand Crimp Tool for Crimp Terminals	0638117400

This document was generated on 04/05/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION