



Blackburn®

Split-Bolt

T&B Catalog Number:

4H
78378620025

Status:

Active

Description:

Type H High Strength Split-Bolt Connector made of Bronze Alloy for Use on Copper Conductors. Conductor Range for Equal Main and Tap 4 Sol.-8 Sol.

Features

Bolt and nut of high-strength corrosion-resistant bronze alloy. Copper pressure bar. Bolt and nut of hex design.

General

Style	Type H
Wire Type	Copper
Material	Bronze Alloy
Conductor Range for Equal Main and Tap 4 Sol.-8 Sol.	
Conductor Range Min. Tap with one Max. 14 Sol. Main	

Dimension Information

A (inches)	17/32
B (inches)	0.235
C (inches)	23/32
D (inches)	1 1/16

Packaging

T&B Inner Pack	100
Package in Units	600
T&B Sold in UOM	Each
T&B Weight Per UOM	7.08 lbs. per 100

Notes

UL recognizes solid and stranded conductor configurations for sizes #8 and smaller and stranded configurations only for sizes #6 and larger.

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E9809

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com