

Main

Range of product	C120 C60 DPN ID IDPN
Device short name	MX + OF
Product or component type	Shunt trip release with OC contact
Signal contacts composition	1 C/O
Control circuit voltage	110...415 V AC 50/60 Hz 110...130 V DC
9 mm pitches	2

Complementary

Local signalling	Action indicator
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Height	82.5 mm
Width	18 mm
Depth	68 mm
Connections - terminals	Clamp terminal 1 cable(s) 2.5 mm ² flexible
Wire stripping length	9 mm
Tightening torque	1 N.m

Environment

Standards	EN/IEC 60947-5-1
Product certifications	ASEFA ASTA KEMA LCIE
Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...85 °C

Contractual warranty

Period	18 months
--------	-----------