

PICCOLO PC C 65 G



Sample photo

Order symbol: PC C 65 G
Product nbr: 8724305
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002037
EI. number:
Finland: 3423405
Denmark: 8212001514
Italy: 7201020
Sweden: 2536807
Norway: 2536505

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:		140	80	65	Ingress Protection (EN 60529): IP 66/67
inch:		5.5	3.1	2.6	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate		Halogen free (DIN/VDE 0472, Part 815): Yes	
Base colour:		RAL 7035		UV resistance: UL 508	
Cover colour:		RAL 7035		Flammability Rating (UL 746 C 5): UL 746C 5V	
Cover screws material:		Polyamide		Glow Wire Test (IEC 695-2-1) °C: 960	
Cover screws colour:		Grey		NEMA Class: NEMA 1, 4X, 6, 6P, 12, 13	
Gasket material:		Polyurethane			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C		Germanischer Lloyd (GL)	
Continuous:		-40 ... 80 °C		Underwriters Laboratories	
Short term:		-40 ... 250 °F		Fimko	
Continuous:		-40 ... 175 °F		Europe EN 62208: 2003	
Accessories:					UL Canada
C-MP		Mounting plate		Gost R	
CHM-3		DIN-35 Mounting rail			
FP 22040		Wall fastening lug (2 pcs)			

PICCOLO 140x80x65-85

