

# Extended-Distance/Quiet Cable with Non-removable EMI/RFI Hoods, Stranded, DB9, Straight-Wired, 9 (4 1/2 Pairs)—All Pins, 50-ft. (15.2-m), MF

MFG Part Number: EGM12D-0050-MF



## Description

Extended-Distance/Quiet Cable with Non-removable EMI/RFI Hoods, Stranded, DB9, Straight-Wired, 9 (4 1/2 Pairs)—All Pins, 50-ft. (15.2-m), MF

## Quick Facts

- Made for short runs in extra-noisy environments.
- 100% foil shield plus a tinned copper-braid.
- 24 AWG stranded copper conductors.
- Guaranteed for life!

## Further Details

- Protect your data from end to end with a 100% foil shield plus an 85% tinned copper-braided shield.
- Ideal for industrial environments. EMI/RFI-resistant hoods stop damaging noise where cables are most vulnerable—at the connection.
- In extra-quiet environments, use these cables for long runs—up to 500 feet (152.4 m) at 9600 bps.
- In extra-quiet environments, use it for long runs up to 500 feet (152.4 m) at 9600 bps.
- Also available with removable hoods.

## Technical Specifications

**Cable Construction** — PVC

**Conductor Gauge** — 24 AWG (7 x 32) stranded copper

**Mutual Capacitance** — 12 pF/ft.

**Resistance** — 30 ohms/1000 ft.

**Shield** — 100% aluminium foil, 85% tinned copper braid

RoHS — Yes