

# Doro PhoneEasy® 622

## Stylish clamshell mobile phone with weather and remote management

Stylish camera phone with loud and clear sound. All details and functions are designed for ease of use, and you can even send video messages as easily as you take and share photos. Other features include direct memories and SMS button, charging cradle, Bluetooth®, weather forecasts and remote management with Doro Experience® Manager.

- ✔ Easy to use camera with flash
- ✔ Extra loud and clear sound
- ✔ Manage content remotely



### STANDARD FEATURES ON MOST DORO PHONES

- |  |   |   |   |   |   |   |   |   |   |
|--|---|---|---|---|---|---|---|---|---|
|  |  |  |  |  |  |  |  |  |  |
| Loud and clear sound   | Adjustable frequency  | Hearing Aid Compatible  | Separated large keys  | Adjustable contrast and theme   | Adjustable text size  | Security functions  | Ergonomic design  | Easy menu handling  | Hide unwanted functions   |

# Doro PhoneEasy® 622



## Main features

Speakerphone	✓
Backlit keypad	✓
Talking keys	✓
Startup wizard	✓
FM-radio	✓
Weather function	✓
Assistance button	✓
Torch	✓
Calculator	✓
Games	✓
Calendar with reminder	✓
Wake up alarm	✓
ICE (In Case of Emergency)	✓

## Camera

Camera resolution (megapixel)	2
Camera flash	✓
Video recording	3gp (240x320 & 144x176)

## Memories

One touch memories	2
Phonebook positions	500

## Handset unit display

External display	✓
Display size (H x W mm)	49*36
Optional display modes optimised for visually impaired users	✓
Adjustable font size	✓

## Doro Experience manager, web based remote handling

Add, remove or edit contacts	✓
------------------------------	---

Vibrating ringer	✓
------------------	---

## Acoustics

Receiving maximum level (dB RLR)	35
Hearing Aid Compatibility Rating	T4/M4 (3G), T4/M3 (2G)
Maximum ringer volume (dB(A) at 1 metre)	>83
Volume settings	7

## Ergonomic sound™

Tone control	✓
--------------	---

## SMS

SMS key	✓
Predictive text	✓
Adjustable multi-tap timing	✓
MMS	✓

## Ergonomics

Hide unwanted functions	✓
Handset size (mm)	102*52*19
Handset weight including batteries (g)	104

## Cables & Connections

Headset outlet (3.5mm)	✓
------------------------	---

## Powering handset unit

Standby time (up to hours)	380
Talk time (up to hours)	10
Battery included (type)	800mAh Li-ion
Universal Charging solution (UCS)	✓

## Technology

# Doro PhoneEasy® 622



Add, edit or remove calendar events ✓

Add or remove pictures ✓

Add, remove or edit daily reminders ✓

## Sounds & Signals

Polyphonic ringtones 22

GSM (band) 900/1800/1900

3G ✓

Bluetooth® protocol 2.1

Memory card type Micro SD

SAR 0.483