

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [08-55-0124](#)
Status: **Active**
Overview: [KK® 396 RPC Connector System](#)
Description: [KK® High Pressure Crimp Terminal 7879, 22-30 AWG, Reel Selective Gold \(Au\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	7879
Application	Signal
Crimp Quality Equipment	Yes
Overview	KK® 396 RPC Connector System
Packaging Alternative	08-55-0129 (Loose)
Product Name	KK® High Pressure
UPC	800753614185

Physical


Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.117/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm²	N/A

Material Info

Old Part Number [7879-1\(P208\)](#)

Reference - Drawing Numbers

Product Specification [PS-7879](#)
 Sales Drawing [SD-7879](#)



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[7879Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool	0011030022
Terminator Die	0011402251
Insertion Tool	0638120000
Hand Crimp Tool	0638190800
Mini-Mac™	0638915100
Applicator	